

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560174-031 Grandbury

Partner timeless elegance with a pinch of coastal vibe with this wall lantern. A beautiful black square frame crafted from corrosion-proof composite polymer material features a half loop on top of the structure. The light fixture's clear glass panes allow the lantern to complement other farmhouse and coastal decor for an overall beautiful, welcoming look. DURASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- The light fixture's clear glass panes allow the lantern to complement other farmhouse and coastal décor for an overall beautiful, welcoming look.
- A beautiful black square frame crafted from corrosion-proof composite polymer material features a half loop on top of the structure.
- Partner timeless elegance with a pinch of coastal vibe with this wall lantern.
- Ideal for any foyer, bedroom, entryway, porch, or patio in transitional, farmhouse, coastal, or vintage electric settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust, corrosion, and fading.
- Measures 5-1/2-inch width by 11-7/8-inch height.
- Uses one medium base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear glass Panel



Width: 5-1/2 in
Height: 11-7/8 in
Depth: 6-1/2 in
H/CTR: 3-1/8 in

Clear glass Panel
Width: 5 in
Height: 8-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 60 W max. Medium Base or LED equivalent	CETLus Wet Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	E26 base Porcelain socket	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 6.875" ht., 1" depth	120 V		