



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560175-020 Grandbury

Grandbury Collection One-Light Transitional Antique Bronze Outdoor Wall Lantern with DURASHIELD

**Category:** Outdoor

**Finish:** Antique Bronze (Unfinished)

**Construction:** injection-Molded Plastic Construction

**Glass/Shade:** Clear Glass Panel



Width: 7-1/8 in  
Extends: 8 in  
Height: 13-5/8 in  
H/CTR: 3-1/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 6.825" ht., 1" depth		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket Fully dimmable with dimmable bulbs	