

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560182-031 Chatsworth

Imagine sleepy vintage streets and old-world architecture with this wall lantern's new take on a traditional design. An elongated lantern silhouette boasts an antique charm as brass tone accents highlight vintage character and inspiration. Clear glass panes grant a nod to the lantern's transitional demeanor.

- Clear glass panes grant a nod to the lantern's transitional demeanor.
- An elongated lantern silhouette boasts an antique charm as brass tone accents highlight vintage character and inspiration.
- Imagine sleepy vintage streets and old-world architecture with this wall lantern's new take on a traditional design.
- Ideal for any entryway, porch, or patio.
- Perfect for transitional and new traditional settings.
- Measures 7-1/2-inch width by 14-1/4-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Outdoor

**Finish:** Black (Painted)

**Construction:** Cast Aluminum Construction

**Glass/Shade:** Clear glass panel



Width: 7-1/2 in  
Height: 14-1/4 in  
Depth: 8-1/2 in  
H/CTR: 11-3/4 in

Clear glass panel  
Width: 4-7/8 in  
Height: 8-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or LED equivalent	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	E26 base Porcelain socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 9" ht., 1" depth	120 V		