

Z-1080 LED

Wall vertical only Mounted • Wet Location Listed **PROGRESS LED**

Description:

Z-1080 LED Collection Black Two-Light Large LED Outdoor Sconce

Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W., 23.25 in Ht., 0.75 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

| | |
|------------------------|------------------------------------|
| Number of Modules | 2 |
| Input Power | 11 W |
| Input Voltage | 120 V |
| Input Frequency | 60 Hz |
| Lumens/LPW (Delivered) | 847/38 (LM-79) |
| CCT | 3000 K |
| CRI | 90 CRI |
| Life (hours) | 54000 (L70/TM-21) |
| EMI/RFI | FCC Title 47, Part 15, Class B |
| Warranty | 5-year Limited Warranty |
| Labels | cCSAus Wet Location Listed |
| | Meets California Title 24 JA8-2019 |


P560211-031-30



Dimensions:

Width: 5 in
Depth: 3 in
Height: 23-1/2 in
H/CTR: 11-3/4 in

White Acrylic Diffuser
Width: 4-1/8 in
Height: 22-5/8 in



P560211-031-30

Dimming Notes:

P560211-031-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Leviton_IPI06-1LZ

Leviton_SureSlide 6674

Lutron_Nova T VTELV-300

Lutron_Diva DVELV-300P

Lutron_Ariadni AYCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.