



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

# P560267-031

## Stature

Stature Collection 1-Light Textured Black Clear Glass Transitional Outdoor Small Wall Lantern Light

**Category:** Outdoor

**Finish:** Textured Black (Powder Coat)

**Construction:** Aluminum Construction

**Glass/Shade:** Clear Glass Panel, Clear Glass Panel



Length: 6 in  
Extends: 5-3/8 in  
Height: 11-1/2 in  
H/CTR: 5-1/4 in

Clear Glass Panel  
Width: 0-1/8 in  
Height: 10-3/16 in

Clear Glass Panel  
Width: 0-1/8 in  
Height: 11.06 in

| MOUNTING  | ELECTRICAL                | LAMPING                    | ADDITIONAL INFORMATION     |
|---|---------------------------|----------------------------|----------------------------|
| Wall mounted  | 6 inches of wire supplied | Quantity:<br>one 60 W max. | cCSAus Wet Location Listed |
| Mounting backplate for outlet box included  | 120 V                     | E12 base Porcelain Socket  | 1-year Limited Warranty    |
| Backplate covers a standard 4" recessed outlet box: 4.312" W., 11.12" ht., 0.5" depth |                           |                            |                            |