

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560286-020 Walcott

Walcott Collection One-Light Antique Bronze with Brasstone Accents Clear Glass Transitional Outdoor Wall Lantern Light

**Category:** Outdoor

**Finish:** Antique Bronze (Painted) with Brasstone accent

**Construction:** Aluminum Construction

**Glass/Shade:** Clear Glass Flat Panels



Width: 7-1/8 in  
Extends: 7-3/8 in  
Height: 14 in  
H/CTR: 3-1/4 in

Clear Glass Flat Panels  
Length: 4.75 in  
Width: 0-1/8 in  
Height: 8-11/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.5" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	