



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560288-031 Trafford Non-Metallic Lantern

Trafford Non-Metallic Lantern Collection One-Light Textured Black Frosted Shade Traditional Outdoor Wall Lantern Light

Category: Outdoor

Finish: Textured Black

Construction: Polycarbonate Construction

Glass/Shade: Frosted Acrylic

MADE IN USA



Width: 5 in
Extends: 6-3/4 in
Height: 11-1/2 in
H/CTR: 4-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Wet Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.62" W., 6.87" ht., 0.62" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	