

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560297-108 Point Dume™-Seamoor

Point Dume Seamoor Oil Rubbed Bronze Outdoor Wall Lantern

**Category:** Outdoor

**Finish:** Oil Rubbed Bronze (Painted)

**Construction:** EPMM Construction

**Glass/Shade:** Clear Glass Flat Square/Rectangular, Clear Glass Flat Square/Rectangular



Width: 11 in  
Extends: 6 in  
Height: 12-5/8 in  
H/CTR: 7-1/2 in

Clear Glass Flat Square/Rectangular  
Width: 8-1/16 in  
Height: 9-7/16 in

Clear Glass Flat Square/Rectangular  
Width: 4 in  
Height: 9-7/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 8.5" W., 9.62" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	