

Point Dume™-Wakecrest-LED

Wall Mounted • Wet Location Listed PROGRESS LED

Description:

Point Dume Wakecrest LED Galvanized Finish Outdoor Wall Lantern

Specifications:

- Clear Etched Glass Square/Rectangular
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant
- Dark Sky compliant

Performance:

Number of Modules	1
Input Power	6 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	266/41.56 (LM-79)
CCT	2700 K
CRI	90 CRI
Life (hours)	45000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed

P560300-141-27



Dimensions:

Width: 6-1/2 in
Extends: 3-7/8 in
Height: 6-5/8 in
H/CTR: 3-13/16 in

Clear Etched Glass Square/Rectangular
Width: 2-3/8 in
Height: 0-1/8 in

P560300-141-27

Dimming Notes:

P560300-141-27 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_DVELV-303P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.