

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560303-141 Point Dume™-Dunemere

Point Dume Dunemere Galvanized Finish Outdoor Wall Lantern

Category: Outdoor

Finish: Galvanized Finish (Painted)

Construction: EPMM Construction

Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 6-5/8 in
Extends: 5-7/8 in
Height: 14 in
H/CTR: 9-1/4 in

Clear Glass Flat Square/Rectangular
Width: 4-1/8 in
Height: 9-7/8 in

Clear Glass Panel
Width: 4-1/2 in
Height: 12-3/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---------------------------|---|----------------------------|
| Wall mounted | 6 inches of wire supplied | (1) Medium Base (E26) Socket | cETLus Wet Location Listed |
| Mounting backplate for outlet box included | 120 VAC | Lamp Type T10 | 5-year Limited Warranty |
| Canopy covers a standard 4" recessed outlet box: 4.75" W., 12.25" ht., 0.75" depth | | Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs | |