

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560304-31M Point Dume™-Dunemere

Point Dume Dunemere Matte Black Outdoor Wall Lantern

Category: Outdoor
Finish: Matte Black (Painted)
Construction: EPMM Construction
Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 8 in
Extends: 7-1/8 in
Height: 16 in
H/CTR: 10-1/8 in

Clear Glass Flat Square/Rectangular
Width: 5-1/8 in
Height: 11-1/16 in

Clear Glass Panel
Width: 5-3/16 in
Height: 14-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.81" W., 13.9375" ht., 0.875" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	