

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560305-108 Point Dume™-Hook Pond

Point Dume Hook Pond Oil Rubbed Bronze Outdoor Wall Lantern

Category: Outdoor
Finish: Oil Rubbed Bronze (Painted)
Construction: EPMM Construction
Glass/Shade: Clear with Silver Mesh Print Glass Flat Square/Rectangular,
 Clear with Silver Mesh Print Glass Flat Square/Rectangular



Width: 6-1/4 in
 Extends: 5-1/4 in
 Height: 16-1/2 in
 H/CTR: 11 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular
 Width: 4-1/2 in
 Height: 8-7/8 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular
 Width: 3-3/8 in
 Height: 8-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type G25	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.56" W., 10.5" ht., 0.8125" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	