

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560305-141 Point Dume™-Hook Pond

Point Dume Hook Pond Galvanized Finish Outdoor Wall Lantern

**Category:** Outdoor

**Finish:** Galvanized Finish (Painted)

**Construction:** EPMM Construction

**Glass/Shade:** Clear with Silver Mesh Print Glass Flat Square/Rectangular,  
Clear with Silver Mesh Print Glass Flat Square/Rectangular



Width: 6-1/4 in  
Extends: 5-1/4 in  
Height: 16-1/2 in  
H/CTR: 11 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular  
Width: 4-1/2 in  
Height: 8-7/8 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular  
Width: 3-3/8 in  
Height: 8-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type G-25	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.56" W., 10.5" ht., 0.8125" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	