

Project:			
Fixture Type:			
Location:			
Contact:			

P5675-20 Cylinder

5" up/down cylinder/outdoor lantern in Antique Bronze. with heavy duty aluminum construction and die cast wall bracket. Powder coated finish. Wet location listed when used with P860045 top cover lens.

- · Antique Bronze finish.
- · Powder coat finish.
- Ideal for a wide variety of interior and exterior applications.
- · Die-cast aluminum wall brackets and heavy duty aluminum framing.
- Wet location listed when used with P860045 top cover lens (sold separately)

Category: Outdoor

Finish: Antique Bronze (powder coat paint) **Construction:** cast aluminum Construction



Width: 5 in Height: 14 in Depth: 7-7/8 in H/CTR: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: two 75 W max. PAR-30 or BR-30	cCSAus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E26 base porcelain sockets	
back plate covers a standard 4" recessed outlet box: 4.5" W.,			