

One-Light Outdoor

 Ceiling flush mounted • Damp location listed 

Description:

6" flush mount cylinder. The P5741 Series are ideal for a wide variety of interior and exterior applications including residential and commercial. The Cylinders feature a 120V alternating current source and eliminates the need for a traditional LED driver. This modular approach results in an encapsulated luminaire that unites performance, cost and safety benefits.

Specifications:

- White (-30) (powder coat paint)
- Die cast and extruded aluminum Construction
- Ideal for a wide variety of interior and exterior applications.
- Die-cast aluminum construction with durable powder coated finish
- 1600 lumens 45 lumens/watt (delivered)
- 3000K color temperature, 90+ CRI
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1
Input Power	29.3w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1600/45 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed Meets California Title 24 high efficacy requirements for outdoor use only

P5741-30/30K

Images:



Dimensions:

Diameter: 6"

Height: 12"

P5741-30/30K**Dimming Notes:**

P5741 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova NTELV-300

Lutron Verti VTELV-600

Lutron MAELV-600

Lutron SPELV-600

Leviton AWRMG-EAW

Leviton 6615-P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.