

## Valera LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

### Description:

Valera Collection LED Two-Light LED Wall Lantern

### Specifications:

- Matte White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Chassis covers a standard 4" recessed outlet box: 5.25 in W, 16.0625 in ht., 0.6875 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Number of Modules	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	640/41 (LM-79)
CCT	3000 K
CRI	90+ CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed

## P5806-12930K9



### Dimensions:

Width: 5-5/8 in  
Height: 16 in  
Depth: 4 in  
H/CTR: 8 in

Matte White Acrylic Diffuser  
Length: 5.375 in  
Width: 3-3/4 in  
Height: 15-15/16 in

# P5806-12930K9

## Dimming Notes:

---

P5806-12930K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Nova T NTELV-300

Lutron\_Vierti VTELV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.