

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5837-71

Nottingham

Scrolling cast arms, fluted bodies and acorn accents. Clear seeded glass compliments this cast aluminum and brass constructed three-light wall lantern.

Category: Outdoor

Finish: Gilded Iron (painted)

Construction: Cast aluminum construction

Glass: Water seeded glass



Width: 10"
Height: 26"
Depth: 13"
H/CTR: 9-1/2"

Glass: 8" dia.
Height: 8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting hardware for outlet box included</p> <p>Back plate covers a standard 4" hexagonal recessed outlet box</p> <p>5" W., 13-5/8", 1-1/8"</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 3</p> <p>60W Candelabra Base</p> <p>Candelabra phenolic sockets</p>	<p>cCSAus Wet location listed</p> <p>1 year warranty</p> <p>Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available</p>