

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5875-20WB

Ashmore CFL

Ashmore collection features quill scrolled arms, decorative finials with etched water glass in a die-cast aluminum construction. One-light CFL wall lantern. Bulb included. Antique Bronze finish.

- Antique Bronze finish.
- Etched water seeded glass curved panels.
- Quill-scrolled arms and decorative finials.
- Meets California Title 24.

Category: Outdoor

Finish: Antique Bronze (powder coat paint)

Construction: Die-cast aluminum Construction, solid brass interior components

Glass/Shade: Etched, water seeded glass curved panels



Width: 8-3/8"
Height: 16-5/8"
Depth: 10-1/2"
H/CTR: 4-1/2"

Glass

Width: 5-13/16"
Height: 6.-15/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Back plate covers a standard 4" octagonal recessed outlet box</p> <p>4.5" W., 9" ht.</p>	<p>Pre-wired</p> <p>6 feet of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>One 26w max. GU-24(included)</p> <p>GU24 base plastic socket</p>	<p>cCSAus Wet location listed</p> <p>1 year warranty</p> <p>Meets California Title 24 high efficacy requirements for outdoor use only</p>