

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5895-108

Penfield

Smooth contemporary curves highlighted by a clear glass exterior surrounding an opal glass interior. Aluminum and brass construction. One-light wall lantern.

Category: Outdoor

Finish: Oil Rubbed Bronze (painted)

Construction:

Glass: Outer clear glass cylinder, Inner white opal glass cylinder



Width: 6-1/2"

Height: 9-3/4"

Depth: 8-1/2"

H/CTR: 5"

Glass: Outer 5" dia., Inner 3-7/8" dia.

Height: Outer 8-1/8", Inner 8-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included 5", 9-3/8"ht., 1" depth	Pre-wired 6" of wire supplied 120V	Quantity: 1 100W Medium Base Medium porcelain socket	cCSAus Wet location listed 1 year warranty Companion fixtures are available