

Endorse LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

Endorse Collection One-Light Small Wall Lantern

Specifications:

- Clear Glass Beveled Panels (Top)
- Clear Glass Beveled Panels (Bottom)
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.5 in W., 5.875 in ht., 0.875 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Dark Sky compliant

Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed

P6056-3130K9



Dimensions:

Width: 6-3/4 in
 Height: 12 in
 Depth: 7-5/8 in
 H/CTR: 3-1/4 in

Clear Glass Beveled Panels (Top)
 Length: 4.5625 in
 Width: 0-3/16 in
 Height: 2-9/16 in

Clear Glass Beveled Panels (Bottom)
 Width: 0-3/16 in
 Height: 5-7/8 in



P6056-3130K9

Dimming Notes:

P6056-3130K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_Vierti VTELV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.