

## Wish LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

### Description:

Wish Collection One-Light Medium LED Wall Lantern

### Specifications:

- Etched White Linen Glass Cylindrical Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.6875 in W., 6.25 in ht., 1 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Yes, per photometry (not registered with IDA)

### Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,211/71.2 (LM-82)
Lumens/LPW (Delivered)	234/14.1 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed


## P6085-3130K9



### Dimensions:

Width: 9 in  
Height: 12-1/2 in  
Depth: 10-1/2 in  
H/CTR: 3-1/8 in

Etched White Linen Glass Cylindrical Diffuser  
Width: 5-5/16 in  
Height: 7-3/8 in



# P6085-3130K9

## Dimming Notes:

---

P6085-3130K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Nova T NTELV-300

Lutron\_Vierti VTELV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.