


Incandescent

# **Complete Squares**Non-IC

Recessed

Type -30**TG** P6414 □

	Finish	Dimensions (Inches)					
Catalog No.	White	Lamping	Α	В	C	D	
P6414	-30TG	1 (m) 100w	8	14-1/	4 4-1/4	9-1/2	
			Ceilir	Ceiling opening 8-1/8			



## **Specifications:**

#### Wiring

- Universal junction box with snap out sides
- Grounding pigtail
- 1/2" & 3/4" knock outs for rigid or BX fittings

### Construction

- Steel construction throughout
- Maximum ceiling thickness is 1"
- Four clips furnished for ceiling installation
- Outlet box assembly removable from inside unit for electrical inspection

#### **Bar Hangers**

- Must be ordered separately (P8716-01)
- 26" bar hangers span 24" T-bar spacing

#### Electrical

- Medium based porcelain socket with nickel plated brass screw shell
- Socket mounted in fixed position
- Pre-wired

## **Labeling**

- Non-IC rated
- UL-CUL listed for damp locations

#### Trim

- Steel construction, painted white
- Flat white glass
- Trim installs with torsion springs and fits tight to ceiling

Progress Lighting Post Office Box 5704 Spartanburg, South Carolina 29304-5704