

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P6539-31

Cadence CFL

The Cadence collection one-light hanging lantern has a decorative and fashion oriented design with modern classic styling. The etched glass pillar diffuser inside the clear water seeded glass gives off a soft glow of light. Uses GU24 base compact fluorescent lamps for energy efficiency. Cast aluminum, powder coated frame in Black.

- Uses GU24 base compact fluorescent lamps for energy efficiency.
- The etched glass pillar diffuser inside the clear water seeded glass gives off a soft glow of light.
- Cast aluminum, powder coated frame in Black.
- Meets California Title 24.

Category: Outdoor

Finish: Black (powder coat paint)

Construction: Aluminum Construction

Glass/Shade: Water seeded glass



Diameter: 10"
Height: 24-5/8"
Overall Ht. W/Chain: 100"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting bracket for outlet box included 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.9375" W., 1.4375" ht., 4.9375" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: One 26w max. GU-24 GU24 base socket	cCSAus Damp location listed 1 year warranty Meets California Title 24 high efficacy requirements for outdoor use only