

# LED Step Lights

 Wall Mounted • Wet Location Listed **PROGRESS LED**

## Description:

Led Step Light

## Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

## Performance:

Input Power	4.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	114/25.332 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed Meets California Title 24 JA8-2016

# P660004-020-30



Shown in vertical installation



Shown in horizontal installation

## Dimensions:

Length: 4-7/8 in (Mounted Horizontal)  
 Height: 3-1/8 in  
 Depth: 1-1/2 in

Mounted inside wall/J-box  
 Width: 2-5/8 in  
 Height: 1-5/8 in  
 Depth: 1-1/8 in

# P660004-020-30

## Dimming Notes:

---

P660004-020-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.