

## LED Step Lights

Wall Mounted • Wet Location Listed **PROGRESS LED**

### Description:

Led Step Light

### Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Input Power	4.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	114/25.32 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed Meets California Title 24 JA8-2016

## P660004-031-30



Shown in vertical installation



Shown in horizontal installation

### Dimensions:

Length: 4-7/8 in (Mounted Horizontal)  
Height: 3-1/8 in  
Depth: 1-1/2 in

Mounted inside wall/J-box  
Width: 2-5/8 in  
Height: 1-5/8 in  
Depth: 1-1/8 in

# P660004-031-30

**Dimming Notes:**

---

P660004-031-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls:**

---

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.