

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P6825-30

Step Lights

One metal housing with two shatter-resistant white acrylic louver faceplates for both sides of a stud wall, 3-1/2" to 4-1/2" thick. Illuminates two areas with one light. For indoor and protected outdoor use.

- White powder coated steel.
- White acrylic louver faceplate.
- Gasketed for light leak prevention.
- One 7 or 9w 2-pin twin compact fluorescent.
- Louvers have linear baffles to direct all light downward.
- Interior wiring compartment.
- 1/2" knock-outs for conduit or BX connections.
- Units must be mounted at least 3" from any insulation.
- Brackets for direct mounting to wall board are provided.
- The same brackets accept P8716-01 hanger bars, if required, for new construction.
- 120V NPF magnetic ballast.
- G23 base lampholder.
- Multiple units can be wired together without the need of separate junction boxes.
- Wall opening = 5" x 7-5/8"

Category: Step Lights

Finish: White (White)

Construction: Steel construction

Glass/Shade: White acrylic diffusers



Width: 8-3/4"
Height: 5-7/8"
Depth: 3-1/2"

Back box

Width: 7.625 in

Height: 5 in

Depth: 3.5 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|-----------------|--------------------|---|--|
| Ceiling mounted | Pre-wired 120 V | Quantity: One 9w max. 2-pin, twin compact fluorescent G23 base plastic socket | UL-CUL Damp location listed 1 year warranty |