

incandescent

Complete Round Housing & Trim Heater Light

Non-IC


Type -16TG

Recessed

P6952

6-7/8 ceiling opening

| | Finish | Lamping | | | | |
|----------------|-------------------|--------------------|---------------------|----|-------|--------|
| Catalog No. | Satin Aluminum | | Dimensions (Inches) | | | |
| | | | Α | В | C | D |
| P6952 | -16TG | 1 R-40 250w Heater | 8-3/8 | 13 | 7-3/4 | 7-3/4" |



Specifications:

Wiring

- Universal junction box with snap out
- Removable housing for field inspection of wiring
- Ground pigtail
- 1/2" & 3/4" knock outs for rigid or BX fittings
- Rated for 8 #12 90 degree conductors (4 in, 4 out)

Construction

- Steel construction
- Maximum ceiling thickness 1-1/2"
- Full wrap around plaster frame
- Suitable for remodel application as per instruction sheet provided with fixture

Bar Hangers

- 26" bar hangers span 24" T-bar spacing
- Captive
- Lock to secure housing

Electrical

- Medium base porcelain socket with nickel-plated brass screw shell
- Socket mounted in fixed position
- Pre-wired

Labeling

- Non-IC rated
- UL-CUL Damp location listed and feed through branch wiring

<u>Trim</u>

- Aluminum construction with light satin finish
- Open trim
- Trim installs with coil springs and fits tight to ceiling

Rev. 08/14

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607