

Hide-a-lite

Undercabinet Mounted • Damp Location Listed **PROGRESS LED**

P700026-028-CS

Description:

Hide-A-Lite Collection 18" LED 5-CCT Linear Undercabinet Light

Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 17.27 in W., 0.12 in ht., 3.02 in depth
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	6.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	457/70 (LM-79)
CCT	2700 K
	3000 K
	3500 K
	4000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019



Dimensions:

Width: 17.5 in
 Depth: 3-1/4 in
 Height: 1.05 in



P700026-028-CS

Dimming Notes:

P700026-028-CS is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

IDevices IDEV009

Leviton_Trimatron 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron Caseta Wireless

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.