

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Linear fluorescent

P7001-30EBS

Undercabinet

Mount easily under cabinets and shelves, over a desk, in kitchens or any work area. All have a white acrylic diffuser and white baked enamel housing. 120/277V HPF electronic ballast.

Width: 3-7/8"
Length: 24-1/4"
Height: 1-5/8"

Category: Undercabinet

Finish: White (baked enamel)

Construction: Steel construction

Glass: White acrylic diffuser

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Flush mounted</p> <p>Chassis covers a standard 4" hexagonal recessed outlet box</p>	<p>Pre-wired</p> <p>120/277V HPF electronic</p> <p>120/277V</p>	<p>Quantity: 1</p> <p>17W F17T8</p> <p>Bi-pin twist-in ceramic lamp holders</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p>