

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



Linear fluorescent

# P7008-30DVEBS

## Undercabinet

Mount easily under cabinets and shelves, over a desk, in kitchens or any work area. All have a white acrylic diffuser and white baked enamel housing. 120/277V HPF electronic ballast.

**Category:** Undercabinet

**Finish:** White (baked enamel)

**Construction:** Steel construction

**Glass:** White acrylic diffuser

**Width:** 3-15/16"

**Length:** 36-3/16"

**Height:** 1-3/8"

**Glass:** 1-5/8"

**Length:** 36"

**Height:** 1-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Flush mounted</p> <p>Chassis</p>	<p>Pre-wired</p> <p>120V/277V HPF electronic</p> <p>120/277V</p>	<p>Quantity: 1</p> <p>25W F25T8</p> <p>Bi-pin twist-in ceramic lamp holders</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p>