

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Fluorescent

P7022-30EBWB

Hide-a-Lite III

8w and 13w T5 Linkable in White finish.

- Horizontal (facing down or up) or vertical mounting
- Open keyslots allow quick installation on pre-installed screws
- Linking and low-profile, with high brightness T-5 lamps. An on/off rocker switch is included.
- Each fixture includes a T-5 fluorescent lamp that has a 10,000 hr average lamp life and 3000K color temperature.
- Non dimmable.
- Extruded aluminum housing with a white acrylic diffuser.
- Slotted holes allow easy mounting through housing. Tool-less electrical compartment entry.
- These energy-efficient low profile fixtures have an integral on/off rocker switch, and a white acrylic diffuser. Available in 4 lengths, they can be linked together with the HAL3 Quick-link cables (P8733-p8743). The P8740 hardware Junction box must be used to power the HAL3 T-5 fluorescent products.

Width: 3-1/4"

Length: 34"

Height: 1-1/8"

Category: Undercabinet

Finish: White (White)

Construction: Extruded aluminum Construction, polycarbonate end caps

Glass/Shade: White acrylic diffuser

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Undercabinet mounted Complies with "Americans with Disabilities Act" - ADA	Pre-wired 120 V	Quantity: One 8w max. F8T5(included) G5 Miniature Bi-Pin base ceramic lamp holders One 13w F13T5 (included) G5 Miniature Bi-Pin base	CSA1 year warranty