

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Linear fluorescent

P7231-15EB

Linear Fluorescent Bath

White acrylic diffuser with a flat top and curved face in sleek polished metal end caps using a 120-277V HPF electronic ballast. This fixture uses long-life electronic ballast with safety quick disconnect of ballast for superior performance and reliability. Bi-pin twist-in base lamp holders. Quick connect for ease of installation. UL Damp Location listed makes this a great fixture for use in bathrooms and powder rooms.

- Chrome finish.
- White acrylic diffuser.
- Sleek polished metal end caps.
- Superior performance and reliability.
- Meets California Title 24.

Width: 36-1/2"

Height: 3-1/4"

Depth: 5-1/4"

Length: 36"

Height: 3-1/8"

Category: Bath & Vanity

Finish: Polished Chrome (Plated)

Construction: Steel construction

Glass/Shade: White acrylic diffuser

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Fixture can be installed with glass facing up or down</p> <p>Chassis covers a standard 4" octagonal recessed outlet box</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120-277 V</p>	<p>Quantity:</p> <p>Two 25w max. F25T8</p> <p>Bi-pin twist-in base lamp holders</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Meets California Title 24 high efficacy requirements</p>