

## LED CTC COMM

Flush-Mount Mounted • Damp Location Listed PROGRESS LED



### Description:

One-Light Urban Bronze LED close-to-ceiling. Surface mount round with clean modern lines and white acrylic diffuser. DC LED light engine with 3200 delivered lumens at 3000K and 90+ CRI.

### Specifications:

- White acrylic diffuser
- Urban Bronze finish.
- Steel construction.
- Dimmable to 10% brightness with many Forward and Reverse Phase dimmers.
- 3000k color temperature.
- TM-21 54,000 hour life.
- Meets California Title 24 - JA8 - 2016.
- 3,200 lumens (delivered).
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" recessed outlet box: 31.125 in W., 0.5 in ht., 31.125 in depth
- Ceiling pan
- 6 in of wire supplied

### Performance:

Number of Modules	1
Input Power	52 W
Input Voltage	120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	3,200/61.5 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cULus Damp Location Listed ENERGY STAR® qualified Meets California Title 24 JA8-2016


# P7252-17430K9



### Dimensions:

Diameter: 31-1/4 in  
Height: 6-1/2 in

White acrylic diffuser  
Width: 29-1/2 in  
Height: 4-1/2 in



# P7252-17430K9

## Dimming Notes:

---

P7252-17430K9 is designed to be compatible with many Forward and Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Leviton AWRMG-EAW

Lutron N-600

Lutron DVCL-253P-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.