

Linear Cloud

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

Description:

51" LED Linear Cloud

Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- 23.9761 in W., 3.25 in ht., 4.223 in depth

Performance:

Number of Modules	1
Input Power	40 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,989/76 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	52000 (L70/TM-21)
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016


P7279-3030K9



Dimensions:

Length: 51 in
 Width: 10-1/4 in
 Height: 3-1/4 in

White Acrylic Diffuser
 Length: 51 in
 Width: 10-1/4 in



P7279-3030K9

Dimming Notes:

P7279-3030K9 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.