

Project:
ixture Type:
ocation:
iontact:

# **LED Strips**

Wall or ceiling Mounted • Damp Location Listed PROGRESS LED

## **Description:**

Two-Foot LED Strip Light

# **Specifications:**

- · White Polycarbonate Diffuser
- · Dimmable to 10% brightness (See Dimming Notes)
- · Mounting backplate for outlet box included
- 6 in of wire supplied

### **Performance:**

Number of Modules	1				
Input Power	20 W				
Input Voltage	120 V				
Input Frequency	60 Hz				
Lumens/LPW (Delivered)	1,600/80 (LM-79)				
CCT	3000 K				
CRI	90 CRI				
Life (hours)	50000 (L70/TM-21)				
EMI/RFI	Meets FCC Title 47, Part 15 Class B				
Warranty	5-year Limited Warranty				
Labels	cCSAus Damp Location Listed				
	Meets California Title 24 JA8-2016				

D	73	0	0	0	0	-0	7	0	-3	
		V	V	V	V			V		U

#### **Dimensions:**

Length: 23-11/16 in Width: 2-1/8 in Height: 2-7/16 in Depth: 2-1/8 in





# **LED Strips**

Wall or ceiling Mounted • Damp Location Listed PROGRESS LED

#### **Dimming Notes:**

P730000-030-30

P730000-030-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron\_Diva DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.