

# Drums And Clouds

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

## Description:

One-Light 13-1/2" LED Flush Mount

## Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 12.8125 in W., 0.875 in ht., 12.8125 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

## Performance:

Number of Modules	1
Input Power	22.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,025/90 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	36000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	ETL Damp Location Listed
	Meets California Title 24 JA8-2016

# P730002-030-30



## Dimensions:

Diameter: 13-9/16 in  
 Height: 4-1/8 in

White Acrylic Diffuser  
 Width: 13-9/16 in  
 Height: 3-3/4 in



# P730002-030-30

## Dimming Notes:

---

P730002-030-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVCL-253P

Lutron\_Caseta Wireless

Lutron\_Toggler TGCL-153PH

Lutron\_Ariadni AYCL-153P

Lutron\_NTLV-600

Leviton\_SureSlide 6674

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.