

LED Wraps

Wall or ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

Four-Foot LED Wrap Light


Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Mounting backplate for outlet box included
- 6 in of wire supplied

Performance:


Number of Modules	1
Input Power	40 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	3,400/85 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2016

P730012-030-30



Dimensions:

Length: 47-3/8 in
 Width: 2-15/16 in
 Height: 6-3/16 in



P730012-030-30

Dimming Notes:

P730012-030-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.