

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Circline fluorescent

# P7372-30

## Hard-Nox

Two-light flush mount with white acrylic diffuser mounts to baked enamel ceiling pan. Twist on installation with a single locking thumb screw. UL approved for damp locations. Rapid start 120V NPF ballast. Ceiling or wall mount. ADA compliant when wall mounted. Uses one FC12T9 32W and one FC8T9 22W lamps.

- Two-light flush mount.
- White acrylic diffuser mounts to baked enamel ceiling pan.
- Twist on installation with a single locking thumb screw.
- Ceiling or wall mount.
- UL approved for damp locations.
- Ceiling or wall mount.

**Category:** Outdoor

**Finish:** White (baked enamel)

**Construction:** Steel Construction

**Glass/Shade:** White acrylic cloud diffuser



**Diameter:** 13-7/8"

**Height:** 3-1/8"

**Glass**

**Width:** 13-7/8"

**Height:** 2-3/8"

| MOUNTING                                                                                                                                                                                                                            | ELECTRICAL                                                     | LAMPING                                                                                                      | ADDITIONAL INFORMATION                         |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|------------------------------------------------|
| Wall or ceiling mounted<br>Mounting screws for outlet box included<br>Complies with "Americans with Disabilities Act" - ADA<br>Ceiling pan covers a standard 4" octagonal recessed outlet box<br>12.75" W., 0.25" ht., 12.75" depth | Pre-wired<br>6" of wire supplied<br>120V NPF rapid start 120 V | Quantity:<br>One 32w max. FC12T9<br>4-pin circline base lamp holders<br>One 22w FC8T9<br>4-pin circline base | UL-CUL Damp location listed<br>1 year warranty |