

DATE:	TYPE:	
NAME:		
PROJECT:		



Circline fluorescent

P7380-30

Acrylic Square

One-light 19 inch fixture with rectilinear form and a white acrylic diffuser. Can be wall or ceiling mounted. Twist on easy installation with a single locking thumb screw. Diffuser has a swing-on latch for easy lamping. Uses T-8 bulbs.

White acrylic diffuser.

Swing action latches on diffuser.Can be wall or ceiling mounted.

Category: Close-to-Ceiling Finish: White (White)

Construction: Steel Construction Glass/Shade: White acrylic diffuser Width: 19" Height: 3-1/8"

Glass Width: 19" Length: 19" Height: 2-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or ceiling mounted Mounting strap for outlet box included Complies with "Americans with Disabilities Act" - ADA Ceiling pan17.8583" W., 0.7244" ht., 17.8583" depth	Pre-wired 6" of wire supplied 120V NPF120 V	Quantity: One 32w max. FC12T9 4-pin circline base lamp holders 40w FC16T9 4-pin circline base	UL-CUL Damp location listed 1 year warranty