

Intrinsic

Ceiling Mounted • Damp Location Listed PROGRESS LED



Description:

Intrinsic Collection 7" Antique Bronze Flush Mount LED Adjustable Eyeball Ceiling Fixture

Specific tions:

- Dimmable to 10% brightness (See Dimming Notes)
- Mounting strap for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	15.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	950/61 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P810029-020-30



Dimensions:

Length: 7-1/4 in
Diameter: 7-1/4 in
Height: 1-1/2 in

**Dimming Notes:**

P810029-020-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

Eaton SAL06P

IDevices IDEV009

Leviton 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P810029-020-30