


Type	
-01	
P8643 🗌	

## **Dimensions (Inches)**

Catalog No.	Lamping	A B
P8643-01	10 - 42w (4-pin), Quad, Triple,	9-1/2 2-3/8
	2D and Twins	Case Height = 1-1/2"



# **Specifications:**

### General

- Will cold start and operate all specified lamps
- Long-life, 3.6 volt high-temperature Ni-Cad battery
- Test switch and charge light included in an easy-to-install switch box
- 5-year warranty
- 90-minute emergency operation
- Battery is recyclable through RBRC call 1-800 8BATTERY
- Can be used with any compact fluorescent fixture utilizing compatible lamps

## Construction

- Painted steel case
- All leads enclosed in flex conduit

#### Lamps

- 10 42w 4-pin Rapid Start Compact lamps, incl.: twin tube, triple tube, quad, 2D & straight
- Initial lumen output is 650 for one lamp

#### Mounting

- For remote mounting only
- Maximum mounting distance is 50 feet or 1/2 AC ballast manufacturer's recommended maximum mounting distance, whichever is less

## **Electrical**

- Dual voltage 120/277V, 60 Hz
- Meets or exceeds all NEC and NFPA Life Safety Code Emergency Lighting Requirements

## <u>Labeling</u>

• UL listed

Progress Lighting Post Office Box 5704 Spartanburg, South Carolina 29304-5704