

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P900011-009 Ridgecrest

Infuse an abundance of sophisticated versatile light to an commercial or residential setting with this brushed nickel one-head track light fixture. A multi-directional lamp head provides design flexibility and illuminates typically hard-to-reach areas. The round ceiling plate, thin metal bar, and light base are coated in a beautiful brushed nickel finish. The lamp head features a crisp frosted glass shade for soft, general ambient light.



- The lamp head features a crisp frosted glass shade for soft, general ambient light.
- The round ceiling plate, thin metal bar, and light base are coated in a beautiful brushed nickel finish.
- A multi-directional lamp head provides design flexibility and illuminates typically hard-to-reach areas.
- Ideal for any sitting room, hallway, or foyer.
- Perfect for transitional or modern settings.
- Measures 5-inch width by 6-3/8-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Directionals
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched glass Cylindrical Shade



Width: 5 in
 Height: 6-3/8 in
 Depth: 7-1/2 in

Etched glass Cylindrical Shade
 Width: 3-3/4 in
 Height: 4-1/2 in



MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity: One 60 W max. Medium Base or LED equivalent	CCSAus Damp Location Listed
Canopy 5" W., 1.18" ht., 5" depth	6 inches of wire supplied 120 V	E26 base socket	1-year Limited Warranty