

# PCVT SERIES

Wet Location LED

## Specifications:

### Features:

- Rugged die-cast aluminum housing with removable cast aluminum guard included
- Gray powder paint provides corrosion resistance and clean finish
- Frosted glass lens distributes light evenly without any LED brightness or glare
- Vandal resistant set screws attach globe to fixture body
- 120-277V, 50/60Hz 11 w, 250 mA, 70 LPW
- 1 high powered COB LED delivers 757 lumens
- 4100K, 80 CRI
- PCVTW (wall mount) covers up to 4.5" j-box with ½" x 14 NPS threaded conduit entry and four side conduit entries
- PCVTS (ceiling/pendant) accommodates traditional ½" x 14 NPS threaded top conduit entry and four side conduit entries

### Application:

The PCVTS is intended to be mounted on a ceiling or as a pendant while the PCVTW is intended to be mounted on a wall. Both can be applied to entries, corridors, tunnels, service areas, elevator wells, stairwells or retro-accent applications.

### Compliances:

UL 1598 listed for use in wet locations (unit is not rated for use in hazardous locations), IP66 rated.

### Warranty:

5 year warranty (Terms and Conditions Apply)

### Images:


PCVTS-LED



PCVTW-LED




### Dimensions:



**PCVTS-LED**

**A:** 5.2" (132mm)

**B:** 10.37" (263mm)



**PCVTW-LED**

**A:** 7.34" (186mm)

**B:** 11.0" (280mm)

**C:** 5.2" (132mm)

### Catalog number:

Base	Mount	Lamp
PCVT	S - Ceiling/Pendant W - Wall	LED - LED, 11 Watts