



\* Representative image

## Rod, Expanding/Cross-Plate Anchor, 5/8in X 7ft Ovaleyeye

by CHANCE Utility  
Catalog ID: PS6417

Expanding/Cross-Plate Anchor Rod 0.625" (15.9 mm) Diameter Rod, 7' (2134 mm) long with Ovaleyeye.

- Drop forged Ovaleyekinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

## Product Details

### General

Coating	Galvanized
Eyenuit Style	Ovaleyeye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb
Type	Anchor Rod
UPC	096359073130

### Dimensions

Length	84.000 in
Rod Diameter	0.625 in
Weight	7.448 lb

### Logistics

Pallet Quantity	100 EA
Standard Package	5

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)