



* Representative image

Cutout, Temporary 27Kv

by CHANCE Utility
Catalog ID: PSC6010342

TEMPORARY CUTOUT-27KV-100AMPS-POLYMER, To provide fuse protection during live-line maintenance, the temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick. Brass stud at lower end accepts clamp on temporary tap jumper. Insulated bushing and hot parts are from Chance Type C-Polymer cutouts: Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze. Fusetube must be fitted with fuselink rated no larger than 100 amps.

Product Details

General

Style	100 Amp Fuse Tube
UPC	096359391500

Dimensions

Weight	12 lb
--------	-------

Electrical Ratings

Voltage Rating	27000 V
----------------	---------

Conductor Related

Conductor Diameter (Main) - Maximum	1.16 in
-------------------------------------	---------

Logistics

Pallet Quantity	32 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com