



\* Representative image

# Cutout, Temporary W/ Solid Blade

by CHANCE Utility  
Catalog ID: PSC6010344

CUTOUT,TEMPORARY 27kV POLY SOLID BLADE, To provide fuse protection during live-line maintenance, the temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick. Bronze stud at lower end accepts clamp on temporary tap jumper. Orange 1.25"-diameter Epoxiglas® member fitted with two EPDM-rubber storm skirts serves as the cutout bushing. Cutout hot parts are identical to Chance Type C cutouts: Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze. Fusetube should be fitted with fuselink rated no larger than 100 amps.

## Product Details

### General

Style	300 Amp Solid Blade
UPC	096359356288

### Dimensions

Weight	18 lb
--------	-------

### Electrical Ratings

Voltage Rating	27000 V
----------------	---------

### Conductor Related

Conductor Diameter (Main) - Maximum	1.16 in
-------------------------------------	---------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com