



\* Representative image

# Cutout, 15Kv Temporary Pvt Lvr

by CHANCE Utility  
Catalog ID: PSC6010345

CUTOUT, TEMPORARY 15KV POLY LINEBREAK, To provide fuse protection during live-line maintenance, the temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick. Brass stud at lower end accepts clamp on temporary tap jumper. Insulated bushing and hot parts are from Chance Type C-Polymer cutouts: Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze. Fusetube must be fitted with fuselink rated no larger than 100 amps.

## Product Details

### General

|       |                                  |
|-------|----------------------------------|
| Style | 100 Amp Fuse Tube w/ Pivot Lever |
| UPC   | 096359397809                     |

### Dimensions

|        |         |
|--------|---------|
| Weight | 11.5 lb |
|--------|---------|

### Electrical Ratings

|                |         |
|----------------|---------|
| Voltage Rating | 15000 V |
|----------------|---------|

### Conductor Related

|                                     |         |
|-------------------------------------|---------|
| Conductor Diameter (Main) - Maximum | 1.16 in |
|-------------------------------------|---------|

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)