



* Representative image

PT061150007SS

by Acme Electric

Catalog ID: PT061150007SS

Prop65_Cancer&Reproductive

Panel Tran Zone Power Centers - Single Phase, 480 - 120/240V, 7.5kVA, Snap In Breakers, 304 Stainless Steel

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

Product Details

General

ANFC Taps	-
BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Breaker	ED42B025L (25A)
Primary Voltage	480
Product Category	Panel-Tran Zone Power Centers
Secondary Breaker	Q240 (40A)
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503089675
Winding Material	CU
kVA	7.5

Dimensions

Height	32.13 in
Length	11 in
Weight	160 lb
Width	15.88 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 1062