



* Representative image

PT061150025SS

by Acme Electric

Catalog ID: PT061150025SS

Prop65_Cancer&Reproductive

Panel-Tran Zone Power Centers - Single Phase, 480 - 120/240V, 25kVA, Snap In Breakers, 304 Stainless Steel

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

Product Details

General

ANFC Taps	-
BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Breaker	ED42B090L (90A)
Primary Voltage	480
Product Category	Panel-Tran Zone Power Centers
Secondary Breaker	Q2125 (125A)
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503090572
Winding Material	CU
kVA	25

Dimensions

Height	41.88 in
Length	13.5 in
Weight	330 lb
Width	17.88 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 1062