



PT0B1150025SS

by Acme Electric
Catalog ID: PT0B1150025SS

Panel Tran Zone Power Centers - Single Phase, 480 - 120/240V, 25kVA, Bolt In Breakers, 304 Stainless Steel

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

Product Details

General

| | |
|----------------------|-------------------------------|
| ANFC Taps | - |
| BNFC Taps | 2 |
| Construction | Encapsulated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Wall |
| Primary Breaker | ED42B090L (90A) |
| Primary Voltage | 480 |
| Product Category | Panel-Tran Zone Power Centers |
| Secondary Breaker | B2125 (125A) |
| Secondary Voltage | 120/240 V |
| Taps % Steps | 5% |
| UL Insulation Class | 180°C |
| UPC | 047503090398 |
| Winding Material | CU |
| kVA | 25 |

Dimensions

| | |
|--------|----------|
| Height | 41.88 in |
| Length | 13.5 in |
| Weight | 330 lb |
| Width | 17.88 in |

Electrical Ratings

| | |
|------------------|-------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 480 V |

Certifications and Compliance

| | |
|--------------|-------------|
| CSA Standard | C22.2 No 47 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 1062 |